Who seed one with the seed one of the seed one

Whether you're a professional using a flashlight for work or security, an outdoor enthusiast who takes it camping, or an occasional user wanting it for emergencies at home or on the road, the ML300LX™ D-cell LED is The Light For All Your Needs.



With the familiar "QuickClikTM" system users can, within the "General" function set, choose Full Power (maximum Lumens): Low Power (up to 143 Lumens); or Eco Mode - a super power saving mode that yields up to 58 Lumens with greatly extended run-time. As shown, there are three additional function sets - Outdoor; Law Enforcement; and Military - each offering a different set of functions invoked in a different sequence, for quickest access to the functions the particular user prefers. The IMPROVED, fasterhandling "Quick FocusTM" system now adjusts from spot to flood with about a ¼ turn of the head.

Function Sets

Function Set	1 GENERAL (Default)	2 OUTDOOR	3 LAW ENFORCEMENT	4 TACTICAL
1 CLICK	Full Power	Full Power	Momentary	Momentary
2 CLICKS	Low Power	Low Power	Full Power	Full Power
3 CLICKS	Eco	Strobe	Eco	Strobe

ML300LX

MAGLITE

Packaging Options





Blister pack

Chipboard box

Features & Benefits











Available Colors





Green



Urban Grav

Stealth Matte Finish

• Aggressive Knurled Design

TECHNICAL SPECIFICATIONS



2-Cell D

- Type Full Size
- Lumens **524 lm**
- Beam Distance 366m
- Peak Beam Intensity **33573cd**
- Barrel Diameter 1.55 in. / 38.1 mm
- Batteries (Alkaline) Not Included
 Weight With Batteries 20 oz. / 566.99g
- Water-Resistant Yes
- Drop Resistance 1m
- Technology **LED**
- Length 9.125 in. / 231.77 mm
- Run Time, High/Low/Eco 6h30min/20h/69h
- Head Diameter 2.25 in. / 57.15 mm
- Rechargeable No
- Blister Size 13 H x 5 W x 2.25 D in.
- Chipboard Box Size 9.44 H x 2.16 W x 2.16 D in.



3-Cell D

- Type Full Size
- Lumens **625 lm**
- Beam Distance 406m
- Peak Beam Intensity 41200cd
- Barrel Diameter 1.55 in. / 38.1 mm
- Batteries (Alkaline) Not Included
- Weight With Batteries 26.4 oz. / 748.43g
- Water-Resistant Yes
- Drop Resistance 1m
- Technology LED
- Length 11.75 in. / 298.45 mm
- Run Time, High/Low/Eco **16h/77h/117h**
- Head Diameter 2.25 in. / 57.15 mm
- Rechargeable No
- Blister Size 14.91 H x 5 W x 2.25 D in.
- Chipboard Box Size 11.78 H x 2.16 W x 2.16 D in.



MAG INSTRUMENT, INC. • 2001 South Hellman Ave., Ontario, CA 91761 909-947-1006 • 800-289-6241 • www.maglite.com • email: salesdesk@magmail.com



^{*} Under Mag Instrument's Continuous Product Improvement strategy, we do make in-line changes to existing products that can impact performance. The ANSI test results shown here are current as this spec sheet goes to press. Consult product packaging/labeling for any updated performance figures.