



PIN OUT

	CN1 (568B)	CN2 (568B)
WHITE	1	1 WHITE
ORANGE	2	2 ORANGE
WHITE	3	3 WHITE
GREEN	6	6 GREEN
BLUE	4	4 BLUE
WHITE	5	5 WHITE
WHITE	7	7 WHITE
BROWN	8	8 BROWN
SHELL	Braid	
		SHELL

NOTE:

1. ELECTRICAL TEST:100% OPEN SHORT, MISS WIRE TEST
2. TEST LIMIT:ISO11801 Channel Class E
3. Working temperature:-10°C ~ + 60°C
4. Plug Contacts durability:750 cycles min
5. RoHS2.0 AND REACH compliant
6. Spray WORD:
CAT. 6 S/FTP 27AWG 250MHz LOZH PATCH CORD ISO/IEC 11801 & EN50173 & TIA/EIA 568 C. 2

FILE NO.	B/N	UNO NO.	LENGTH
29212c92i		216322. 01	150+60/-0mm
29212c92		216322. 52	250+60/-0mm
29212c92a		216322. 50	500+60/-0mm
29212c92b		216322. 11	1000+100/-0mm
29212c92c		216322. 03	3000+100/-0mm
29212c92d		216322. 05	5000+100/-0mm
29212c92e		216322. 00	10000+100/-0mm
29212c92f		216322. 15	15000+100/-0mm
29212c92g		216322. 20	20000+100/-0mm
29212c92h		216322. 30	30000+100/-0mm

MATERIAL LIST

③	CABLE	CAT. 6 S/FTP 27AWG (BC*1P+AL-FOIL)*4+BRAID AL-MG JACKET:LOZH OD:6.0±0.2mm WHITE PANTONE 427C	1	
②	Over mold	PVC WHITE (427C)	2	
①	Plug	RJ45 8P8C'S SHIELDED ,THE SHELL PLATED NICKEL, PIN GOLD PLATED 3u" RED/TRANSPARENT	2	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK
ARVIN				
		NEW		2016-02-17 A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

CUSTOMER NO.		CEI Conrad Electronic International (HK) Ltd	ITEM NO.	
PRODUCT NAME	Cat. 6 S/FTP Round Patch cord 27AWG	UNO ITEM NO.	UNIT	MM
DRAWNBY	CHECKBY	APPOBY	DATE	
ARVIN	ALVAN		2016-02-17	