


Keystone Jack

Installing Instruction DN-93501





Strip approximately 30mm of the cable jacket, and separate to 4 pair each

2

T568A

Pin 5 White/Blue
Pin 4 Blue
Pin 1 White/Green
Pin 2 Green
Pin 3 White/Orange
Pin 6 Orange
Pin 7 White/Brown
Pin 8 Brown

T568B


Pin 5 White/Blue
Pin 4 Blue
Pin 1 White/Orange
Pin 2 Orange
Pin 3 White/Green
Pin 6 Green
Pin 7 White/Brown
Pin 8 Brown

3



Follow the direction on the colorcoding sticker to position T568A or T568B wiring, separate a little space on proper position and insert the wire pair by pair into each slot


_



Unshielded type

Use 110 or KRONE impact tool to press and cut off each conductor.

5



Insert the IDC cap to fix these wires. Insert the cable tie to tight up the cable jacket and complete the installation.

Shielded type






Slide the cable jacket into Cable Holder.

4




Follow the direction on the color coding sticker to position T568A or T568B wiring, separate a little space on proper position and insert the wire pair by pair into each slot. Use 110 or KRONE impact tool to press and cut off each conductor

5



Insert the cable tie to tight up the cable jacket. Insert the IDC cap to fix these wires.

6



Cover the Full shield, then complete the installation.





(Note: Full shield has to insert into this plastic slot)