

DATASHEET

ESD component box

Item No. 1433012



Dimension

W1: 120x L1: 140x H: 68mm

W2: 50mm & L2: 35mm

Dimension unit: mm (+/-0.5)

Material	Conductive Plastic
Color	Black
Surface Resistance	approx. $10^4 \Omega \sim 10^8 \Omega$
Operating Temperature	-10 ~ +75° C
Storage Temperature	-10 ~ +80° C
Operating Humidity	< 95% RH
Storage Humidity	< 95% RH
Weight of Product.....	approx. 0.08kgs
Tolerance.....	+/- 0.5mm

Distributed by Conrad Electronic SE

This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2016 by Conrad Electronic SE.