

Delock WLAN Twin Antenna 2 x MHF IV 802.11 ac/a/h/b/g/n 5 dBi 150 mm PCB internal self adhesive

Description

This WLAN twin antenna is designed to integrate into your devices with MHF IV connectors. These are two separate antennas with common ground.



Specification

- Connectors: 2 x miniature RF coaxial connector MHF IV (IPEX)
- Frequency range:
 - 2400 ~ 2500 MHz
 - 5150 ~ 5875 MHz
- Gain: 5 dBi
- Impedance: 50 Ohm
- Cable length: 150 mm
- Cable diameter: 1.13 mm
- Cable type: coaxial
- Operating temperature: -10 °C ~ 50 °C
- Dimensions (LxWxH): 61.6 x 7.0 x 1.6 mm

Item No. 89454

EAN: 4043619894543

Country of origin: China

Package: Poly bag


System requirements

- Device with free MHF IV connector

Package content

- Antenna

Images



General	
Suitable for indoor:	yes
Suitable for outdoor:	no
Operating temperature:	-10 °C ~ 50 °C
Interface	
Connection:	2 x MHF IV
Technical characteristics	
Frequency range:	2.400 GHz - 2.500 GHz 5.150 GHz - 5.875 GHz
Gain:	5 dBi
Impedance:	50 Ohm
Power handling:	1 W
VSWR:	2
Physical characteristics	
Cable category:	coaxial cable
Cable type:	1.13
Cable colour:	black
Cable length:	150 mm
Length:	61.6 mm
Width:	7.0 mm
Height:	1.6 mm
Weight:	8 g