

GB Data sheet

Low-voltage connector with switch

Item no. 1434423

Technical data

Suitable for	12 V LED strip
Power input.....	max. 84 W
Switch specifications	2 A, 250 V/AC
	3 A, 125 V/AC
Plug/socket Ø	5.5/2.1 mm (outer/inner)
Cable length	300 mm
Cable Ø	4 mm (outer)
Wire Ø	22 AWG
Mating cycles.....	>3000
Contact plating.....	nickel
Material.....	PVC + ABS
Colour.....	black
Operating temperature	-25 to +80 °C
Operating humidity	10 – 90 % RH
Storage temperature.....	-25 to +80 °C
Storage humidity.....	10 – 90 % RH

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This publication represent the technical status at the time of printing.

Copyright 2022 by Conrad Electronic SE.

1434423_V2_1221_01_PIX_ds