

Technische Daten / Specification

Nennspannung / Rated voltage	12 VAC
Nennstrom / Rated current	0,5 A
Bauart / According to	DIN EN 60238
Anschlüsse / Type of terminals	Schraubanschluss / Screw terminals
Kontakte / Material of terminals	CuZn 37
Kontaktträger / Gehäuse	Harnstoff-Formmasse Typ 131.5 oder Phenolharz-Formmasse Typ 31 / Urea moulding compound Type 131.5 or phenolic moulding compound type 31
Carrying parts / Cover	

Abmessungen / Dimension
