Housing - HC-EVO-B10-SHWS-2SSM32-PLRBK - 1407636

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (http://download.phoenixcontact.com)



Box mounting bases B10, With single locking latch, Material: Polyamide, Cable outlets: 2, Lateral, Height: 74 mm, Cable gland: none, Gland: no, 2x M32, Standard

Article description

One screw connection opening is closed, however can be opened using a screwdriver

Your advantages

- Lower costs than metal version
- Low weight
- Lower risk of condensation
- Both contact insert PE sheets are connected by means of a metal frame integrated in the sleeve housing
- Metal inlays ensure leading PE contact with angled plugs
- Completely corrosion-resistant
- Halogen-free plastic
- Impact test according to IK 08
- Marking label can be attached

Key commercial data

package_quantity	1
GTIN	4046356776981

Technical data

Dimensions

Height	74 mm
Width	57 mm
Length	93 mm

Ambient conditions

Degree of protection of housing (IP)	IP66
Degree of protection of housing (NEMA)	4 (NEMA 250)
Degree of protection of housing (NEMA)	4X (NEMA 250)
Degree of protection of housing (NEMA)	12 (NEMA 250)
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-B10, BB18, DD42, M, K8/24, HV03-I-PT, HC- 3-E...C

Housing - HC-EVO-B10-SHWS-2SSM32-PLRBK - 1407636

Technical data

General

Size	B10
Housing type	Box mounting bases
Color	black
Locking type	With single locking latch
No. of cable outlets	2
Cable exit	Lateral
Screw connection	none
Type of the screw connection	2x M32
Housing material	Polyamide
Seal material	NBR
Material lock	Polyamide
Flammability rating according to UL 94	V0
Connection	One of the two openings for the screw connections is sealed but can be broken open using a screwdriver.

Standards and Regulations

Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202
eCl@ss 9.0	27440202

ETIM

ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Housing - HC-EVO-B10-SHWS-2SSM32-PLRBK - 1407636

Approvals

GL / EAC /

Approval details

GL s

EAC s

Accessories

Full screw connection

HC-K-KV-M32(12-21)BK - 1407673



G-INS-M32-M68N-PNES-BK - 1411136



Seal

HC-B10-SP-RBK - 1407707



Housing latches

Housing - HC-EVO-B10-SHWS-2SSM32-PLRBK - 1407636

Accessories

HC-B10-SL-PLBK - 1407698



Protective cover

HC-B10-BC-HI-PLBK - 1407693



Plug for cable screw gland

HC-K-BS-M32-BK - 1410754



Device marking

US-EMP (20X9) - 0829439



Accessories

REDUC-K-KV-M32/M25 BK - 1410712



Housing - HC-EVO-B10-SHWS-2SSM32-PLRBK - 1407636


Accessories

REDUC-K-KV-M32/M20 BK - 1410725



Drawings

Dimensional drawing



Dimensional drawing

Phoenix Contact 2016 © - all rights reserved
http://www.phoenixcontact.com