



PIN OUT

P1		P2
1	Red	1
2	White	2
3	Green	3
4	Black	4
5	Yellow	8
6	Blue	9
7	DRAIN	7
8	Orange	5
9	Purple	6
	BRAID+DRAIN	Shell

NOTE:

- Electrical test:
 - 100% open short & miss wire test;
 - Insulation resistance:DC 300V 10MΩ;
 - Contact resistance:3Ω Max;
 - Dielectric strength:150V AC/Minute, 1mA.
- Operation temperature:-10℃ ~+60℃
Storage temperature:-20℃ ~ +75℃
Operation humidity:10%~85%
Storage humidity:10%~85%
- PRINT WORD:E258105 兄 AWM 20276 80℃ 30V VW-1 USB 3.0 SUPER SPEED CABLE
- ROHS2.0 and REACH compliant
- PACKING:1PCS/Renkforce giftbox

MATERIAL LIST:

④	OUTER MOLD	Blue pvc	2	
③	INNER MOLD	LD-PE	2	
②	USB AM TYPE	USB3.0 A/M 9Pin Type, The Pin Gold Plating , the shell for Nickel Plated	2	
①	CABLE	(1/28AWG BC*1P+1/28AWG BC+WAM)*2+1/28AWG BC*2C+1/28AWG BC*2C+ AEB, PVC jaket/Blue OD:5.5±0.2mm	2	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK

FILE NO.	B/N	UNO ITEM NO.	LENGTH	COLOUR
29212c87c	1456481	713116B.50	500+100/-0MM	Blue
29212c87	1456482	713116B.11	1000+100/-0MM	Blue
29212c87a	1456483	713116B.81	1800+100/-0MM	Blue
29212c87b	1456484	713116B.03	3000+100/-0MM	Blue

CUSTOMER		CN		ITEM NO.	See the chart		
PRODUCT NAME		USB 3.0 AM-AM Cable		UNO ITEM NO.	UNIT	MM	
NEW				2016-01-22	A	DATE	
BY	CHK	REVISION RECORD MODIFICATIONS		DATE	REV.	FERGUS	2021-09-15