

BN 1456482
UNO model no. 713116B,11
Description Connection-Cable, USB3.0, A male -> A male, nickel plated,blue color
specification

- USB 3.2 5Gbps A male to A male
- PIN Gold plated Shell Nickel Plated
- 28AWG+28AWG+24AWG Copper conductor
- Double Shielded (Al-foil+Braid)
- PVC Jacket OD5.5mm Black
- PVC molding without USB logo
- Data Transfer: Up to 5Gbps
- Output voltages :5V DC.
- Output current:900mA

Standards

- Backward compatible with USB2.0 / 1.1/1.0
- Operating Temperature:0℃~45℃
- Storage Temperature:-20℃~ 70℃
- RoHS(EU2015/863) and Reach compliant.

product category USB3.2 Cable
Package VP1-1: 105 x 140(depth : 20mm)
LNK
size of ind packing 105*140*20mm
g.w. of ind packing 68g
size of export carton 500*360*250mm
g.w. of export carton 9,2
qty / ctn : 120

