



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A																									
Supplier Information																																		
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer David W	Contact Title	Product Compliance Engineer for DND																											
Company Unique ID	TE Connectivity	Response Date	2016-04-12	Contact Email	dave.benfer@te.com																													
Contact Phone Number		717-986-3725																																
Legal Statement																																		
Supplier Acceptance	true																																	
Legal Statement																																		
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.																																		
Product																																		
Manufacturer Item number	5103308-8	Amount	3281.6506	Version	-	Identity																												
Manufacturer Item Name	A/L LOW PRO HDR 40P VERT BLACK	Weight Uom	mg	Mfr Site		Authority																												
Date		UOM	Each																															
EUROHS-0508	Product(s) meets EU RoHS requirement without any exemptions																																	
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products																																	
EUREACH-0615	REACH Candidate Substances of Very High Concern ARE NOT Contained in the Product Above the Limits per the Definition within REACH																																	
Product Disclosure																																		
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption																									
Sub-Item	1	040 HOUSING LOPRO HDR				1.0	2636.27	mg																										
Material	2	PA66-GF25				1.0	2636.27	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	3.5	1.0	92.26945	mg																										
Substance	3	Benzenamine, reaction products with aniline hydrochloride and nitrobenzene	Supplier	101357-15-7	4.0	1.0	105.4508	mg																										
Substance	3	Glass, oxide, chemicals	Supplier	65997-17-3	25.0	1.0	659.0675	mg																										
Substance	3	Poly[imino(1,6-dioxo-1,6-hexanediyl)imino-1,6-hexanediyl]	Supplier	32131-17-2	61.5	1.0	1621.30605	mg																										
Substance	3	Phosphorus	Supplier	7723-14-0	6.0	1.0	158.1762	mg																										
Sub-Item	1	BAND ASSY .0245 SQ POST .493 15 AU				40.0	16.134515	mg																										
Material	2	Gold Plate				40.0	0.205088	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	40.0	6.1526E-4	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.20447	mg																										
Material	2	Gold Plate				40.0	0.025715	mg																										
Substance	3	Gold	Supplier	7440-57-5	99.7	40.0	0.02563786	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.3	40.0	7.7145E-5	mg																										
Material	2	Tin Plate				40.0	0.184642	mg																										
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	40.0	3.6928E-4	mg																										
Substance	3	Tin	Supplier	7440-31-5	99.73	40.0	0.18414	mg																										
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.07	40.0	1.2925E-4	mg																										
Material	2	Brass Wire				40.0	15.19	mg																										
Substance	3	Copper	Supplier	7440-50-8	71.5	40.0	10.86085	mg																										

Substance	3	Beryllium	Supplier	7440-41-7	0.0010	40.0	1.519E-4	mg	
Substance	3	Zinc	Supplier	7440-66-6	28.0226	40.0	4.25663	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.05	40.0	0.007595	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	40.0	1.519E-4	mg	
Substance	3	Iron	Supplier	7439-89-6	0.05	40.0	0.007595	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.1	40.0	0.01519	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.0099	40.0	0.00150381	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	40.0	0.001519	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.05	40.0	0.007595	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	40.0	7.595E-4	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	40.0	7.595E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	40.0	0.03038	mg	
Material	2	Nickel Plate				40.0	0.52907	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	40.0	0.00105814	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	40.0	5.2907E-4	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	40.0	0.52748	mg	