

■ SPECIFICATION

Dimension	As per drawing below in mm
Type	External drive type element
Resonant Frequency (KHz)	3.8±0.5
Input Voltage (Vp-p/max.)	30
Resonant Impedance (Ω/max.)	200
Capacitance (pF)	25,000 ± 30% at 100 Hz
Operating Temperature (°C)	-20 ~ +60
Storage Temperature (°C)	-20 ~ +70
Base Material	Brass

■ Dimensions (mm)

1. D: 20.0 ±0.1
2. d: 15.0 ±0.3
3. T: 0.28 ±0.1
4. t: 0.15 ±0.05

