

## ■ SPECIFICATION

Dimension	As per drawing below in mm
Type	External drive type element
Resonant Frequency (KHz)	2.9 ± 0.3
Input Voltage (Vp-p/max.)	30
Resonant Impedance (Ω/max.)	300
Capacitance (pF)	25,000 ± 30% at 100Hz
Operating Temperature (°C)	-20 ~ +60
Storage Temperature (°C)	-20 ~ +70
Base Material	Brass

## ■ Dimensions (mm)

1. D: 35.0 ±0.1
2. d: 24.8 ±0.5
3. T: 0.55 ±0.05
4. t: 0.30 ±0.03

