


Product information

97 32 240

Crimping Pliers



- For cutting cables, stripping wire and crimping insulated terminals and heat shrinkable sleeve connectors and non-insulated crimp terminals according to DIN 46234
- With threaded holes for cutting copper and brass screws threaded M 2.6 / M 3 / M 3.5 / M 4 and M 5
- Bolted joint for higher stability and even movement

General	
Article No.	97 32 240
EAN	4003773079491
Pliers	black lacquered
Handles	with multi-component grips
Weight	264 g
Dimensions	240 x 62 x 25 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
	
Application	insulated terminals + cable connectors
Capacity in square millimetres	0.5 — 6.0 mm ²
Number of crimp profiles	3
AWG	20 — 10

technical change and errors excepted