

Lyfe Silver SPECS

Camera:

Weight: 67g / 0.13lbs

Video Recording: 4K/10fps
2.7K/15fps
1440P/30fps
1080P/60fps
720P/120fps

Pixels: 16MP

Voltage: 3.7V / 1050mAh

Storage: External micro SD card up to 64GB (Class 10 Recommended)

Visual Angle 140°

Aperture: f/2.7

Digital Zoom: 4x

Video Recording Format: MP4

Audio Recording Format: WAV

Photo Format: JPEG

Water Resistant: IP68

Water-Resistant Depth: 40 Meter (up to 120 ft)

Storage: Up to 64

| | |
|----------------------------|-------------------------------------------------------------------------------------------------------------|
| Max Video Recording Time: | Up to 3 hours |
| Max Audio Recording Time: | Up to 5 hours |
| Storage Temp: | -20°C ~ 60°C (-4f ~ 140f) |
| Operating Temp: | -10°C ~ 50°C (14f ~ 122f) |
| Dimensions: | 52mm x 26mm x 40mm |
| LCD: | |
| TFT Display: | 1.8" true color TFT (16:9) |
| LED Dot-Matrix Screen: | 25mm x 16mm FSTN (lattice screen) |
| Shooting Modes: | |
| Burst Shooting: | 3, 6, 8 seconds |
| Time Lapse: | 1, 2, 5, 10, 30 seconds |
| Auto Record: | 5, 10, 20 seconds |
| View Angle: | |
| | Wide, Medium, Narrow, Small |
| Video Content Loop: | |
| | On: Video file will be stored in segments of 10 min Off: Video file will be stored in segments of 15 min |

| | |
|-------------------|-----------------|
| Photo Resolution: | 8MP, 12MP, 16MP |
|-------------------|-----------------|

Capture Mode:

| | |
|------------|------------------|
| Fast Shot: | 3p/s, 6p/s, 8p/s |
|------------|------------------|

| | |
|----------------------|---------------------------------|
| Continuous Shooting: | 0.5, 1, 2, 3, 4, 10, 20 seconds |
|----------------------|---------------------------------|

| | |
|-------------|------------------|
| Self Timer: | 3, 5, 10 seconds |
|-------------|------------------|

Charger:

| | |
|--------|---------------|
| Input: | 100~240v 0.5A |
|--------|---------------|

| | |
|---------|--------------|
| Output: | DC 5V 2000mA |
|---------|--------------|

| | |
|----------------------|-----------------|
| Recharging Duration: | About 2.5 hours |
|----------------------|-----------------|
