



10" 1U Rackmount 4-Way Power Strip - German Type

With Power Indicator, No Surge Protection, 1.8 m (5 ft.) Power Cord

Part No.: **714020**

Intellinet basic rack PDUs (Power Distribution Units) provide reliable power distribution via a single input with multiple output receptacles. Our current range is designed to distribute power from low amperage single phase electrical circuits.

Features:

- Outlets: 4-way
- Power input style: left-end single input
- 10" Rack Mountable
- Bracket installation style: rear
- Cable plug: IEC60884
- Control functions: none
- Protection functions: no surge protection
- Shell color & material: black aluminum
- Relative humidity: 10 - 90%
- 3 Year Warranty

Specifications:

- 1U Rackmount
- Socket/outlet standard: IEC60884
- Outlets: 4-way
- Cable specification: standard 1.8 m (5 ft.) power cord
- Size: 254 (L) x 44.4 (W) x 44.4 (H) [mm] / 10 (L) x 1.75 (W) x 1.75 (H) [in]
- Rated Voltage: 125V
- Rated Current: 15A

