



# Vertical Rackmount 12-Way Power Strip - German Type

With Single Air Switch, No Surge Protection

Part No.: **711449**

Intellinet basic rack PDUs (Power Distribution Units) provide reliable power distribution via a single input with multiple output receptacles. Our current range is designed to distribute power from low amperage single phase electrical circuits.

## Features:

- Outlets: 12-way
- Power input style: left-end single input
- Bracket installation style: Rear
- Cable plug: IEC60884
- Control & Protection functions: single air switch
- Shell color & material: black aluminum
- Relative humidity: 10 - 90%
- 3 Year Warranty

## Specifications:

- Socket/outlet standard: IEC60884
- Outlets: 12-way
- Cable specification: standard 1.6 m (5 ft.) power cord
- Size: 640 (L) x 44.4 (W) x 63 (H) [mm] / 25.2 (L) x 1.75 (W) x 2.48 (H) [in]
- Rated Voltage: 250 V AC
- Rated Current: 16 A



