



19" 1.5U Rackmount 6-Way Power Strip - German Type

With Double Air Switch, No Surge Protection, 1.6 m (5 ft.) Power Cord

Part No.: **711432**

Intellinet basic rack PDUs (Power Distribution Units) provide reliable power distribution via a single input with multiple output receptacles. Our current range is designed to distribute power from low amperage single phase electrical circuits.

Features:

- Outlets: 6-way
- Power input style: left-end single input
- Bracket installation style: frontal
- Cable plug: IEC60884
- Control & Protection functions: double air switch
- Shell color & material: black aluminum
- Relative humidity: 10 - 90%
- 3 Year Warranty

Specifications:

- 1.5U Rackmount
- Socket/outlet standard: IEC60884
- Outlets: 6-way
- Cable specification: standard 1.6 m (5 ft.) power cord
- Size: 482.6 x 44.4 x 62 mm (L x W x H) / 19 (L) x 1.75 (W) x 2.44 (H) [in]
- Rated Voltage: 250V AC
- Rated Current: 16A



