



DATASHEET

PVC Twin Cable, 2 x 0.5 mm², 10 M, Brown

Version 07/16

Item no. 1484658

Operating temperature	-20 °C to 70 °C
Jacket, outer dimension.....	PVC 4.0 x 2.0 mm
AWG.....	20
No. of conductors.....	2 x 0.5 mm ²
CCA strand per conductor.....	16 x 0.20 mm
Color.....	Brown
Capacitance conductor.....	210 pF
Voltage.....	Less than 50 V/DC or 75 V/AC
Insulation resistance.....	Min 200 M Ω x km
Operating humidity.....	10 - 90 % RH
Packaging.....	10 meter spool



This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2016 by Conrad Electronic SE.

Distributed Conrad Electronic SE