

DATASHEET

PVC Twin Cable, 2 x 0.5 mm², 25 M, Black

Version 07/16

Item no. 1484671



Operating temperature	-20 °C to 70 °C
Jacket, outer dimension.....	PVC 4.0 x 2.0 mm
AWG.....	20
No. of conductors.....	2 x 0.5 mm ²
CCA strand per conductor.....	16 x 0.2 mm
Color.....	Black
Capacitance conductor.....	210 pF
Packaging.....	25 meter spool
Voltage.....	Less than 50 V/DC or 75 V/AC
Insulation resistance.....	Min 200 M Ω x km
Operating humidity.....	10 - 90 % RH