



DATASHEET

PVC Twin Cable, 2 x 2.5 mm², 25 M, Brown

Version 7/16

Item no. 1484691

Jacket, outer dimension.....	PVC 6.3 x 3.2 mm
No. of conductors.....	2 x 2.5 mm ²
CCA Strand per conductor.....	85 x 0.19 mm
Color.....	Brown
Capacitance conductor.....	115 PF
Packaging.....	25 meter spool
The application.....	48 V Safe Current:20 A
Operating temperature	-20 °C to 70 °C
Electrical resistivity.....	10.52 Ω/KM
Conductivity.....	9.51 x 10+7 S/m
Thermal conductivity.....	2.219 x 10 +2 W/MK
Density.....	2.12 x 10 +3 KG/CBM
Specific weight.....	27.2 KG/KM
Voltage.....	Less than 50 V/DC or 75 V/AC
Insulation resistance.....	Min 200 M Ω x km
Operating humidity.....	10 - 90 % RH



This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2016 by Conrad Electronic SE.