



DATASHEET

PVC Twin Cable, 2 x 4 .0 mm², 10 M, Black

Version 07/16

Item no. 1484692

Jacket, outer dimension.....	PVC 8.0 x 4.0 mm
No. of conductors.....	2 x 4.0 mm ²
CCA Strand per conductor.....	128 x 0.2 mm
Color.....	Black
Capacitance conductor.....	90 PF
Packaging.....	10 meter spool
The application.....	48 V Safe Current:30 A
Operating temperature	-20 °C to 70 °C
Electrical resistivity.....	10.52 Ω/KM
Conductivity.....	9.51 x10 +7 S/m
Thermal conductivity.....	2.219 x 10 +2 W/MK
Density.....	2.12 x 10 + 3 KG/CBM
Specific weight.....	34.3KG/KM
Voltage.....	Less than 50 V/DC or 75 V/AC
Insulation resistance.....	Min 200 M Ω x km
Operating humidity.....	10 - 90 % RH



This data sheet is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com). All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited. This data represent the technical status at the time of printing. Changes in technology and equipment reserved.

© Copyright 2016 by Conrad Electronic SE.