



NOTES:

ELECTRICAL:

- 1. VOLTAGE RATING : 125V AC RMS
- 2. CURRENT RATING : 1.5A mp
- 3. CONTACT RESISTANCE : 100 MILLI OHMS MAX
- 4. INSULATION RESISTANCE : 1000M OHMS/MEN @1500VDC CLASS E
- 5. DIELECTRIC STRENGTH : 750V AC RMS 60Hz, 1MIN
- 6. CAT. 6 PERMANENT LINK : CONFORM TO ANSI/TIA/EIA-568 B. 2-1

ENVIRONMENTAL:

- 1. STORAGE : -40° TO+85°
  - 2. OPERATION : 0° TO+70°
- RJ45 JACK COMPLY TO REQUIREMENTS OF IEC-60603-7-5  
MATES WITH MODULAR PLUG CONFORMING TO FCC PART 68

MECHANICAL

- 1. RJ45 JACK LIFE: 750 TIMES MIN
- 2. IDC LIFE : 200 TIMES MIN

Accessory:

- 1. M3 Screw Set, For Pre-Assembled Ground Wire
- 2. Cable Tie(75X1.9mm)X12Pcs
- 3. Instruction Sheet
- 4. expanded screw X 2 Set

RoHS 2.0 & REACH COMPLIANT

UNO ITEM NO.	Colour
236235	Gray RAL 7035
236245	Black RAL 9005

MATERIAL LIST:

NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK
⑦	Upper Panel Cover	1.2mm thickness Metallic Panel with plastic powder cladding	1	
⑥	Bottom Panel :	1.2mm thickness Metallic Panel with plastic powder cladding	1	
⑤	RJ45 Jack :	Housing-Fireproof PBT UL-94V0 Pin-8P8C 3u" gold plated	12	
④	PCB	1.6mm UL 94V0	2	
③	IDC BODY	Fireproof PC/ABS UL-94V0/With Colour Coded Printing T568A/B	12	
②	IDC PIN	Phosphor Bronze & Tinned	96	
①	IDC TERMINAL	For 22-24 AWG Cable	12	

NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK
		NEW	2015-11-11	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

CUSTOMER		ITEM NO.	
PRODUCT NAME	CAT. 6 MINI 12port STP PATCH PANEL	UNIT	MM
DRAWNBY	CHECKBY	APPOBY	DATE
FERGUS			2015-11-11