



Designation: 16603 101 001

Battery Requirement: 2 x CR2016 lithium button cell

Bulb required: 1pc 5mm cool White LED

Luminous intensity: High: 15 lumens or 31 cd
Low: 8 lumens or 16 cd

Range: 11 m (calculated distance at maximum luminous intensity with an illuminance of 0.25lux).

Weight: 37.6g (with batteries).

Material: Zinc alloy
TPR (Thermal plastic rubber)
All contact parts made of bronze or steel
Contact spring in the screw cap, nickel plated steel.

Dimensions (mm):

A	50
B	24.5
Thickness:	11

**Run Time: 4 hours continuous run time(high mode with included battery)
6 hours continuous run time(low mode with included battery)**

Features:

- Easy push Switch with large size rubber cover (High/Low/Off)
- Super bright 5mm cool white LED
- 10 minutes auto shut-off timer at both high and low mode
- Durable Zinc alloy with chrome plated
- Metal keychain ring
- 1 meter drop test
- 10,000 switch cycle life