

Products » Clearance lamps » FT-045 LED

- 1-functional LED clearance lamp - low power consumption.
- european **E9** homologation for (white,red and yellow light)
- ElectroMagnetic Compatibility - **EMC** certificate
- shock-resistance - **PC** lampshade
- optional polarity connection

In a standard version the lamps are applied to be mounted on the flat surfaces.

Optionally the installation at the grille saver bull bars, bumper guards and body armors can be carried out by using a transparent **FT-045 PG T** rubber gasket that is not included in a standard version of the product.

Lamp functions:

- clearance light (white, yellow and red)
- decorative light (blue and green)

Technical specification:

- supply voltage: **12-36V DC**
- operating temperature: **- 40°C to +55°C**
- lamp is resistant to any weather conditions
- lamp is fully airtight







Power consumption:

- clearance light: **12V/24V = 0,08A/0,08A**

Power consumption / Rated power:

- clearance light: **12V/24V = 1W/2W**



ID/EAN	Photo	Description	Individual package		Carton			Palette		
			qty.	kg	qty.	cm	kg	qty.	cm	kg
FT-045 Z LED		Clearance marker LED lamp, yellow, 2x0.75 mm ² cable (0.5 m).	1	0,06						
FT-045 C LED		Clearance marker LED lamp, red, 2x0.75 mm ² cable (0.5 m).	1	0,06						
FT-045 B LED		Clearance marker LED lamp, white, 2x0.75 mm ² cable (0.5 m).	1	0,06						
FT-045 ZIEL LED		Decorative LED lamp, green, 2x0,75mm ² cable (0,5m).	1	0,06						
FT-045 N LED		Decorative LED lamp, blue, 2x0.75 mm ² cable (0.5 m).	1	0,06						
FT-045 PG T		Rubber gasket (transparent) for FT-045 LED mounted at grille saver bull bars, bumper guards and body armors.	10	0,22						