



Item No.	file No.		Length	Packing
1487676	29212c104	712113.11	1000±20mm	COLOR BOX
1487679	29212c104a	712113.81	1800±30mm	COLOR BOX
1487682	29212c104b	712113.03	3000±50mm	COLOR BOX

NOTE:

1. Electrical test:
 - (1). 100% open short & miss wire test;
 - (2). Insulation resistance: DC 300V 10MΩ ;
 - (3). Contactor resistance: 3Ω Max;
 - (4). Dielectric strength: 100V AC/Minute, 1mA.
2. RoHS 2.0 AND REACH COMPLIANT
3. PRINTING: AWM 80°C 30V VW-1 28AWG×1P 28AWG×2C
4. Operation temperature: -10°C ~ +60°C
 Storage temperature: -20°C ~ +75°C
 Operation humidity: 10%~85%
 Storage humidity: 10%~85%
 Voltage: 5V DC Current: 500mA
5. PACKING: 1PCS/Renkfroce giftbox

MATERIAL LIST:

④	OUTER MOLD	Color For BLACK	2	
③	USB A TYPE	USB A /M Type, The Pin Gold Plating, the shell for Nickel Plating	1	
②	USB A TYPE	USB A /M Type, The Pin Gold Plating, the shell for Nickel Plating	1	
①	CABLE	USB 2.0 (28AWG BC*1P)+(28AWG BC*2C)+AL-FOIL+ BRAID AL-MG PVC JACKET COLOR: BLACK OD: 3.8±0.2mm	1	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT'Y	REMARK

Alvan	ARVIN	revise moulding and Cable PRINTING	2018.06.28	A1
		NEW	2016.06.21	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

CUSTOMER		CN	ITEM NO.		
PRODUCT NAME	USB 2.0 AM/AM			UNIT	MM
DRAWNBY	CHECKBY	APPOBY	DATE		
ARVIN			2016.06.28		