



| file No. | UNO Item No. | Length | Packing |
|------------|--------------|--------------|---------------------------|
| 29212c105 | 712123.33 | 300+20/-0mm | VP1:10.5x14cm (depth:2cm) |
| 29212c105a | 712123.50 | 500+30/-0mm | VP1:10.5x14cm (depth:2cm) |
| 29212c105b | 712123.11 | 1000+40/-0mm | VP1:10.5x14cm (depth:2cm) |

NOTE:

- Electrical test:
 - 100% open short & miss wire test;
 - Insulation resistance:DC 300V 10MΩ;
 - Contact resistance:3Ω Max;
 - Dielectric strength:100V AC/Minute, 1mA.
- RoHS 2.0 AND REACH COMPLIANT
- PRINTING:E258105 兄 AWM 80°C 30V VW-1 28AWG×1P 28AWG×2C
- Operation temperature:-10°C ~+60°C
Storage temperature:-20°C ~ +75°C
Operation humidity:10%~85%
Storage humidity:10%~85%
Voltage:5V DC Current:500mA
- PACKING:1PCS/Renkfroce giftbox

MATERIAL LIST:

| ④ | OUTER MOLD | color For Black | 2 | |
|-----|------------|--|------|--------|
| ③ | USB B TYPE | USB B /M Type, The Pin Gold Plating, the shell for Nickel Plating | 1 | |
| ② | USB A TYPE | USB A /M Type, The Pin Gold Plating, the shell for Nickel Plating | 1 | |
| ① | CABLE | USB 2.0 (28AWG BC*1P)+(28AWG BC*2C)+AL-FOIL +BRAID AL-MG PVC JACKET COLOR:BLACK OD:3.8±0.2mm | 1 | |
| NO. | PARTS NAME | SPECIFICATION STANDARD | QT'Y | REMARK |

| | | | | |
|----|-----|-------------------------------|------------|------------|
| | | | | |
| | | NEW | 2016.06.21 | A |
| BY | CHK | REVISION RECORD MODIFICATIONS | DATE | REV. ARVIN |

| | | | |
|--------------|---------------|--------------|------------|
| CUSTOMER | | ITEM NO. | |
| PRODUCT NAME | USB 2.0 AM/BM | UNO ITEM NO. | UNIT MM |
| DRAWNBY | CHECKBY | APPOBY | DATE |
| | | | 2016.06.21 |