



		Length	Packing
		300+20/-0mm	VP1:10.5x14cm (depth:2cm)
		500+30/-0mm	VP1:10.5x14cm (depth:2cm)
	FI111J€	1000+40/-0mm	VP1:10.5x14cm (depth:2cm)

MATERIAL LIST:

④	OUTER MOLD	color For Black	2	
③	USB B TYPE	USB B /M Type, The Pin Gold Plating, the shell for Nickel Plating	1	
②	USB A TYPE	USB A /M Type, The Pin Gold Plating, the shell for Nickel Plating	1	
①	CABLE	USB 2.0 (28AWG BC*1P)+(28AWG BC*2C)+AL-FOIL +BRAID AL-MG PVC JACKET COLOR:BLACK OD:3.8±0.2mm	1	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT'Y	REMARK

NOTE:

- Electrical test:
  - 100% open short & miss wire test;
  - Insulation resistance:DC 300V 10MΩ;
  - Contact resistance:3Ω Max;
  - Dielectric strength:100V AC/Minute, 1mA.
- RoHS 2.0 AND REACH COMPLIANT
- PRINTING:E258105 兄 AWM 80°C 30V VW-1 28AWG×1P 28AWG×2C
- Operation temperature:-10°C ~+60°C  
Storage temperature:-20°C ~ +75°C  
Operation humidity:10%~85%  
Storage humidity:10%~85%  
Voltage:5V DC Current:500mA
- PACKING:1PCS/Renkfroce giftbox

					CUSTOMER		ITEM NO.	
					PRODUCT NAME		UNIT MM	
					USB 2.0 AM/BM		UNO ITEM NO.	
					DRAWNBY		APPOBY	
					CHECKBY		DATE	
BY	CHK	REVISION RECORD MODIFICATIONS		DATE	REV.	ARVIN		2016.06.21