



file No.	UNO Item No.	Length
29212c107	712152.01	0.15m
29212c107a	712152.33	0.3m

NOTE:

- Electrical test:
  - 100% open short & miss wire test;
  - Insulation resistance:DC 300V 10MΩ;
  - Contact resistance:3Ω Max;
  - Dielectric strength:100V AC/Minute, 1mA.
- RoHS 2.0 AND REACH COMPLIANT
- PRINTING:E258105 兄 AWM 80℃ 30V VW-1 28AWG×1P 28AWG×2C
- Operation temperature:-10℃ ~+60℃  
Storage temperature:-20℃ ~ +75℃  
Operation humidity:10%~85%  
Storage humidity:10%~85%  
Voltage:5V DC
- PACKING:1PCS/Renkfroce giftbox

MATERIAL LIST:

NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK
④	OUTER MOLD	PVC color For Balck	2	
③	USB B TYPE	MICRO USB B /M Type, The Pin Gold Plating, the shell for Nickel Plating	1	
②	USB A TYPE	USB A /M Type, The Pin Gold Plating, the shell for Nickel Plating	1	
①	CABLE	USB 2.0 28AWG (7/0.12BC*1P)+28AWG (7/0.12BC*2C)+AL-FOIL+DRAIN (7/0.12BC)+BRAID (0.12/3/16 AL-MG) PVC JACKET COLOR:BLACK OD:3.8±0.2mm	1	

BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.
		NEW	2016.05.03	A

CUSTOMER	ITEM NO.
PRODUCT NAME	UNIT
USB2.0 AM-MICRO USB BM	MM
UNO ITEM NO.	DATE
712152	2016.05.03
DRAWNBY	APPOBY
ARVIN	
CHECKBY	