



Light is convenient  
LEDinspect<sup>®</sup> PRO

Light is OSRAM

**OSRAM**

**Main benefits of LEDinspect® PRO**

- 3 year guarantee<sup>1)</sup>
- Excellent illumination thanks to long-lasting high intensity LEDs
- Easy to grip and dirt resistant surface
- Inspection and maintenance of vehicles



**OSRAM LEDInspect® PRO**

Order number	Voltage	Watt	Lumen	Color	EAN10	EAN40 <sup>2)</sup>	RRP incl. VAT
LEDIL103	3.4 V	3.5 W	280 lm	6000 K	4052899327351	4052899327368	
LEDIL104	90-250 V	13-15 W	1400 lm	6000 K	4052899970632	4052899970649	
LEDIL105	3.7 V	0.5 W	150 lm (main light) 35 lm (torch light)	6000 K	4052899963825	4052899963832	
LEDIL106	3.7 V	0.5 W	150 lm	6000 K	4052899963849	4052899963856	
LEDIL107	3.7 V	1 W	280 lm (first level) 150 lm (second level) 70 lm (torch light)	6000 K	4052899963863	4052899963870	

1) Refer to [www.osram.com/amguarantee](http://www.osram.com/amguarantee) for precise conditions  
 2) EAN 40 = 4 pcs.

**Easy lamp searching – with the OSRAM lamps navigator:**  
[www.osram.com/applicationguide](http://www.osram.com/applicationguide)

OSRAM GmbH

Head office:

Marcel-Breuer-Strasse 6  
 80807 Munich, Germany  
 Phone +49 89 6213-0  
 Fax +49 89 6213-2020  
[www.osram.com](http://www.osram.com)

