

Hybrid- Window Closer

WIN-CONTROL WS 20.1



Put an end to the permanent
tilt position of your windows!



Technical data:

| | |
|---|------------------|
| Length x width x height: | 147 x 85 x 30 mm |
| Weight: | 380 g |
| Max. operating time: (short time duty) | 3 min |
| Material: | Plastic / white |
| Performance: | Max. 4 W |
| Voltage: | 3 V DC |
| Traction: | 40 N |
| Battery type: | LR6 (AA) |
| Operation mode: | Pull cord |
| MD / RoHS / EMC: | Conform |
| Articel number: | 82924 |
| EAN: | 0040232829246 |

Product properties:

- ✓ Saving of energy, time and costs by controlled ventilation
- ✓ Prevention of mould and enhancement of safety
- ✓ Installation / operation: easy and fast
- ✓ Suitable for all usual tilt and turn windows
- ✓ Closes the window after your time setting from 5 min to 6 h
- ✓ Hybrid drive (spring and electric drive)
- ✓ Wireless operation mode
- ✓ Long battery life / at least 1500 closing operations
- ✓ Optional accessory: rain sensor
- ✓ TÜV Rheinland - building class test mark
- ✓ TÜV Rheinland test mark - "LGA tested Quality"

Ihr Ansprechpartner:



Der Partner für Ihren Erfolg

EMZ Elektro-Marketing-Zentrale GmbH
An den Hirtenäckern 9
63791 Karlstein

Tel. 0 61 88 - 91 450-0
Fax 0 61 88 - 91 450-22
info@emz-stickler.de