



D-2/3AA400 Specifications




Nominal Capacity	400mAh
Nominal Voltage	1.2V
Internal Impedance (at 1000Hz)	< 35mΩ
Charge	
Standard Charge	40mA x 15h
Rapid Charge	400mA x 1.2h
Discharge Cut-off Voltage	1.0V
Max Dimension (with tube)	
Diameter	14.5mm
Height	29.0mm
Weight	14 g
Operating Temperature	
Charge	0 ~ 45°C
Discharge	-20 ~ 60°C
Storage Temperature	
Within 1 month	-5 ~ 35°C
Within 6 months	0 ~ 35°C

Standard charge characteristics



Rapid charge characteristics



Discharge characteristics

