

## Datasheet

Item no.: 1493150 – 25 mm (W) x 33 meter (L) / 1493151 – 50 mm (W) x 33 meter (L)

# Copper Foil Tape



One side can be stick, both side conduct

Backing ..... Copper

Adhesive ..... Non-Conductive Acrylic

Backing Thickness .....  $0.018 \pm 0.005\text{mm}$

Adhesive Thickness .....  $0.032 \pm 0.005\text{mm}$

Total Thickness .....  $0.05 \pm 0.01\text{mm}$

Electrical Resistance .....  $0.03 - 0.05 \Omega$

Adhesive Power ..... 1.5 kg 25mm

Tensile Strength ..... 4.5 kg 25mm

Elongate Rate .....  $> 5\%$

Operation Temperature .....  $0^{\circ}\text{C}$  to  $100^{\circ}\text{C}$