

VOLTCRAFT®

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

"For more than 25 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success."



VERSION 01/17

VC300 A 2-IN-1

POWERBANK WITH JUMP-START FUNCTION

Nº 1496542

The ultra-compact and mobile start-up support with integrated high-performance rechargeable LiPo battery for cars offers you, as of now, instant start-up assistance. When the starter batteries (car, motorcycle, quad / ATV or scooter) are weak, Powerbank jumps in quickly. The integrated safety circuit with overvoltage and undervoltage protection ensures high security. The Powerbank can also charge 2 USB loads like tablets and smartphones simultaneously.

The Powerbank itself is either charged via the power adaptor included or directly via your car's cigarette lighter. Everything comes neatly packaged in a space-saving rugged bag. That way, you will have your mobile start-up support/Powerbank handy at any time.



FEATURES:

Start-up assistance for vehicles with 12 V on-board voltages // Suitable for petrol engines with up to 5.0 litre displacement volume // Suitable for diesel engines up to 2.5 litre displacement volume // 2 Hi-Power USB charging ports //

EQUIPMENT:

LED torch with steady light, flashing light and SOS signal // LED indicators // Connectible ion air purifier // 2 high-power USB-charging ports (1x USB, 1x USB-C™) // Over-charge and discharge protection // Overvoltage, undervoltage protection //

PACKAGE CONTENTS:

Powerbank with jump-start function // Power adapter // Cigarette lighter charging cable // Connection cable with alligator clips // Micro USB cable (approx. 45 cm) // Storage bag // Carabiner // Operating instructions //

TECHNICAL DATA:

Powerbank

Rated voltage Start-up support	12 V/DC
Output current Start-up support	300 A (450 A max.)
Integrated battery	3x LiPo 4000 mAh
Capacity	12 Ah
Cable length pole terminals	50 cm
Output USB	5 V/DC max. 2 A
Output USB-C™	5 V/DC max. 3 A
Powerbank is charged using	Cigarette lighter 12 V or power adaptor
Operating conditions	Temperature 0 to +60 °C rel. humidity 0 – 99 %, not condensing
Product dimensions (L x W x H)	175 x 75 x 34 mm
Weight	454 g

Power adaptor

Operating voltage	100 – 240 V/AC, 50/60 Hz
Output	15 V/DC, 1 A

Legal notice

This data sheet is published by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).
All rights including translation reserved. Reproduction by any method, e.g. photocopy, microfilming, or the capture in electronic data processing systems require the prior written approval by the editor. Reprinting, also in part, is prohibited.
This data sheet represents the technical status at the time of printing.

© Copyright 2017 by Conrad Electronic SE

V2_0117_02/VTP