

REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJH 09/20/05'	~	LJC 09/20/05'
B	料号中增加尺寸DIM. H, E选项	YCH 07/18/08'	~	LJC 07/18/08'
C	ADD P/N CODE	YCH 12/02/13'	~	LJC 12/02/13'
D	ADD P/N CODE	JLZ 07/25/14'	~	

NOTES:

- ELECTRICAL CHARACTERISTICS:
  - CONTACT RESISTANCE: 20mΩ Max. INITIAL.
  - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
  - INSULATION RESISTANCE: 1000MΩ Min.
- ENVIRONMENT CHARACTERISTICS:
  - TEMPERATURE RANGE: -40°C~+105°C.
- PRODUCT NUMBER CODE:

DS1013- X X X X X X - X - X

HOUSING MATERIAL  
 0: PBT UL94 V-0  
 2: PBT UL94 HB  
 4: PA-46

PLATING LEVEL(FOR GOLD ONLY) ©  
 3A: 0.8-1.2u"  
 B: LEVEL B  
 N: LEVEL N

DIM. H TYPE (FOR ELEVATOR ONLY)  
 1: 7.50  
 2: 9.50



DIM. E TYPE (FOR V/T ONLY)  
 1: 3.10  
 2: 8.00

HOUSING COLOR  
 B: BLACK  
 W: WHITE  
 U: BLUE  
 A: GRAY

CONTACT PLATING  
 Si: FULL GOLD FLASH


MOUNTING TYPE  
 S: V/T TYPE  
 R: R/A TYPE  
 E: Elevator TYPE

No. OF CONTACTS  
 06 08 10 14 16 20 24  
 26 30 34 40 50 60 64



Dimension

Position	A	B	C				
06	15.22	13.02	5.08				
08	17.76	15.56	7.62				
10	20.30	18.10	10.16	30	45.70	43.50	35.56
12	22.84	20.64	12.70	34	50.78	48.58	40.64
14	25.38	23.18	15.24	40	58.40	56.20	48.26
16	27.92	25.72	17.78	50	71.10	68.90	60.96
20	33.00	30.80	22.86	60	83.80	81.60	73.66
26	40.62	38.42	30.48	64	88.88	86.68	78.74



GENERAL TOLERANCE		ANGLE TOLERANCE	
X.	±0.60	X.	±5°
.X	±0.38	.X	±3°
.XX	±0.25	.XX	±2°

PROJECTION	TITLE
UNITS	2.54mm BOX HEADER R/A, V/T & ELEVATOR TYPE
SHEET SIZE	A4
SERIES	DS1013 SERIES

DRAWING TYPE	CUSTOMER
SCALE	1:1 SHEET 1 OF 1
DRAWING NO.	C-DS1013-XXXX-X-X-D

**CONNFLY** 晨翔电子有限公司  
**CONNFLY ELECTRONIC CO., LTD**

Tel:86-574-63508787  
 Fax:86-574-63510817  
 E-mail:sales@connfly.com  
 http://www.connfly.com  
 Add:East Industrial Park, Zhongshan Road, Ningbo, Zhejiang, P.R. China  
 P.C.315333