




REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	LJC 02/07/09'	~	LJC 02/07/09'
B	整理图面	YCH 08/18/09'	~	






NOTES:

- Specifications:
  - Contact Resistance: 20mΩ max.
  - Insulation Resistance: 1000MΩ min.
  - Current Rating: 2A.
  - Dielectric withstanding voltage: AC 1000V(r.m.s)/60s.
  - Operating Temperature: -40°C to +105°C
  - Recommend Wave Soldering Temperature: 260°C,5-10s.
- Materials:
  - Contact: Copper alloy
  - Housing: Thermoplastic(UL94 V-0)
- Product Number code:



positions	A	B	C		D
			Female	Male	
64P(2*32)	94.9	90.0	85.0	85.6	78.74
32P(2*16)	54.9	50.0	44.26	44.7	38.10

CONNFLY



GENERAL TOLERANCE	ANGLE TOLERANCE
X. ±0.60	X. ±5°
.X ±0.38	.X ±3°
.XX ±0.25	.XX ±2°

PROJECTION	TITLE
mm	DIN 41612 B TYPE(2ROWS) Vertical Through
SHEET SIZE	SERIES DS1118 SERIES

DRAWING TYPE	CUSTOMER
SCALE	1:1 SHEET 2 OF 3
DRAWING NO.	C-DS1118-XXXXVXX


**晨翔电子有限公司**  
**CONNFLY CONNFLY ELECTRONIC CO. LTD**

Tel:86-574-63508787  
 Fax:86-574-63510817  
 E-mail:sale@zhenqin.com.cn  
 Http://www.connfly.com