

A	Dept	Qty
	DC	1
	ED	1
	IE	1
B	ISO	1
	PD	1
	R&D	1
	SD	1
	QA	1
	QC	1
	QE	1

Notes:

Specifications:

1. Contact Resistance: 20mΩ Max.
2. Insulation Resistance: 1000MΩ Min.
3. Dielectric Withstanding Voltage: 500V AC(rms)
For 1 Minute.
4. Current Rating:2A.
5. Temperature: -40°C~+105°C.

Materials:

1. Contact Material: Copper Alloy.
2. Contact Plating: Gold Plating Over Nickel.
3. Insulator Material: High temp,Black,UL94-V0.

Product Number Code:

Specifications:

1. Contact Resistance: 20mΩ Max.
2. Insulation Resistance: 1000MΩ Min.
3. Dielectric Withstanding Voltage: 500V AC(rms) For 1 Minute.
4. Current Rating: 2A.
5. Temperature: -40°C~+105°C.

1. Contact Material: Copper Alloy.
2. Contact Plating: Gold Plating Over Nickel.
3. Insulator Material: High temp,Black,UL94-V0.

DS1026-01 - X X X X X

Contacts type
V:V/T type

Housing color
B:Black

Contact plating
8: Full gold flash

Connector type
S:Socket

No.of contacts
1x2-1x40



(Series Image-Reference Only)

 晨翔电子有限公司
CONNFLY CONNFLY ELECTRONIC CO. LTD