



## 19" 2U Rackmount 15-Way Power Strip - German Type

With Double Air Switch, 3 m (10 ft.) Power Cord

Part No.: **714051**

Intellinet basic rack PDUs (Power Distribution Units) provide reliable power distribution via a single input with multiple output receptacles. Our current range is designed to distribute power from low amperage single phase electrical circuits.

### Features:

- Outlets: 15-way
- 2U 19" Rackmount unit
- Power input style: left-end single input
- Bracket installation style: frontal
- Control & Protection functions: Double Air Switch
- Shell color & material: black aluminum
- Relative humidity: 10 - 90%
- 3 Year Warranty

### Specifications:

- 2U Rackmount
- Socket/outlet standard: IEC60884
- Outlets: 15-way
- Cable specification: standard 3 m (10 ft.) power cord
- Size: 482.6 (L) x 44.4 (W) x 88.8 (H) [mm] / 19 (L) x 1.75 (W) x 3.5 (H) [in]
- Electrical rating: 250V AC
- Maximum load current: 16 A

