

# Alarm Siren

Product ref.: 142801A0



## Product features

- Audible and visual signal output in alarm cases via piezo speaker and LEDs
- Early warning thanks to loud acoustic signal with  $\geq 90$  dB @ 1 m distance as well red signal LEDs
- Optional acoustic signals for activating or deactivating the security solution
- Different acoustic signals and the alarm duration can be defined
- Tamper contact detects manipulation or unauthorised removal
- Easy and flexible wall or ceiling mounting out of reach for burglars using supplied screws and plugs
- Design similar to smoke alarm
- Can be used with the Home Control Access Point in connection with the Homematic IP app, the Homematic Central Control Unit CCU2 as well as with various partner solutions

## Technical specifications

Supply voltage	3x 1.5 V LR6/mignon/AA
Battery life	2 years (typ.)
Degree of protection	IP20
Ambient temperature	5 to 35 °C
Dimensions (ø x H)	124 x 45 mm
Weight	136 g (including batteries)
Radio frequency	868.3 MHz/869.525 MHz
Typ. open area RF range	250 m

## Logistical data

Product reference	142801A0
EAN code	4047976428014
Short description	HmIP-ASIR
Packing unit	32
Packing dimensions	184 x 140 x 73 mm

## Package contents

Homematic IP Alarm Siren
Ceiling bracket
1,5 V LR06/mignon/AA batteries (3x)
Screws 3.0 x 30 mm (2x) and plugs 5 mm (2x)
User manual