

# Remote Control - 8 buttons

Product ref.: 142307A0



## Product features

- Remote control with eight individually configurable buttons for universal use - buttons can be configured in pairs or individually
- Comfortable control of connected devices e.g. for switching devices or dimming of lights
- One button can simultaneously execute several scenario functions (e.g. move shutters down and switch on the lights at the same time) in connection with the Homematic Central Control Unit CCU2
- Labelling field for button functions at the back side of the remote control can be replaced
- Can be used with the Access Point in connection with the Homematic IP app, the Homematic Central Control Unit CCU2 as well as with various partner solutions

## Technical specifications

Supply voltage	2x 1.5 V LR03/micro/AAA
Current consumption	100 mA (max.)
Battery life	2 years (typ.)
Degree of protection	IP20
Ambient temperature	5 to 35 °C
Dimensions (W x H x D)	46 x 131 x 19 mm
Weight	78 g (incl. batteries)
Radio frequency	868.3 MHz/869.525 MHz
Typ. open area RF range	300 m

## Logistical data

Product reference	142307A0
EAN code	4047976423071
Short description	HmIP-RC8
Packing unit	72
Packing dimensions	184 x 93 x 48 mm

## Package contents

Homematic IP Remote Control - 8 buttons

1.5 V LR03/micro/AAA batteries (2x)

Labelling template

User manual