

# MIDLAND ARCTIC

NEW



## PROGRAMMING SOFTWARE PRG-G15

cod. C1131  
Complete with USB lead for PCs



VHF SEEFUNKGERÄT

## PRACTICAL, RUGGED AND SAFE FOR ALL NEEDS

Midland Arctic is a VHF handheld marine transceiver combining professional technical specifications with robustness and reliability. Functions are all within easy reach, including the button for the instant access to the emergency channel 16. The antenna is removable and thanks to the standard SMA connector it is possible to replace it with other antenna models. The management of the channels and functions is done through the optional programming software.

## SPECIFICATIONS

- IP67 waterproof certification
- Aluminium chassis
- Transmission power: 5W
- High/low power selection (5W/1W)
- 57 international channels
- Programmable channels (through software)
- Backlit wide LCD display
- Instant access to the emergency channel 16
- VOX, SCAN function
- Dual Watch/Triple Watch
- 10 different Squelch levels
- Priority channel
- Keypad lock
- Roger Beep (end of call tone)

- Keypad beep
- Flat battery indicator and automatic battery saver
- Power supply: Li-ion battery pack
- 2-pin Motorola accessory socket

## PACKS AND CODES

1 radio, desktop charger, wall adapter, Li-ion 1600mAh rechargeable battery pack, belt clip  
code C1240

EXPORT VERSION:  
USA/CANADA CHANNELS

## ALLGEMEINES

Kanäle	57 international
Frequenzband TX	from 156.025 to 157.425 MHz
Frequenzband RX	from 156.300 to 162.000 MHz
Betriebstemperatur	from -15°C to +55°C
Size (LxAxP)	115 x 55 x 37mm
Gewicht (nur Gerät)	230 g
Anschlusstyp	Motorola 2,5mm/3,5mm

Programmierbar	Via software (PRG-G15)
Wasserdichtigkeits-Klasse	IP67
<b>SENDER</b>	
Ausgangsleistung	1W o 5W selectable
<b>EMPFÄNGER</b>	
Empfindlichkeit 20dB SINAD	0,3 µV
Audio-Ausgangsleistung	300mW @ 10% THD
Klirrfaktor	<10%