

Datasheet

Item no. : 1511460

V1_10092017_01_en

Waterproof Speaker, 610 mA, dia. 93 mm, Neo, 3W8Ω

1.Item Requirements:

Attribute	Value
1.1 Rate power	3W
1.2 Max power	4W
1.3 Sensitivity	88±3dB(AT 0.1M/0.1W, AT 0.6,0.8,1.0,1.2KHZ)
1.4 Impedance	8 Ω ±15%
1.5 Frequency	Fo~~10KHZ
1.6 Resonance frequency	250±20%
1.7 Distortion rate	≤5%
1.8 Magnet size	Φ12.5*2.0
1.9 Weight	41g±8%
2.0 Size	93*93*22Hmm
2.1 voice coil & Material	Φ13.28mm Paper
2.2 Cone	Waterproof

Datasheet

Item no. : 1511460

V1_10092017_01_en


2.Components:

Basket, Pole-piece, U-yoke , wiring board, magnet, cone, voice coil, spiders, dust cap, down-lead, layering

3.Pictures:



4.Dimensions picture:



Datasheet

Item no. : 1511460

V1_10092017_01_en

5.DB picture:

