

## ESG ESG 8/20 MM GR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com



### Guaranteed long service life: ESG

The multi-colour and multi-format labels have a strong adhesive layer to ensure the best possible adhesion to the underlying surface. Double laminated polyester makes the basic material very thin and yet extremely tear-resistant.

### Your benefits with MultiMark

- Double laminated polyester
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

### General ordering data

Type	ESG 8/20 MM GR
Order No.	<a href="#">2005160000</a>
Version	ESG, Device markers, 20 x 8 mm, Grey
GTIN (EAN)	4050118390735
Qty.	3,000 pc(s).

## Data sheet

### ESG ESG 8/20 MM GR

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Length	20 mm	Length (inches)	0.787 inch
Width	8 mm	Width (inches)	0.315 inch
Net weight	0.06 g		

### General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	Grey	Length	20 mm
Material	Polyester	Number per roll	3,000
Operating temperature range, max.	120 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	V-0	Version	Self-adhesive, halogen-free
Width	8 mm		

### Classifications

ETIM 6.0	EC001288	eClass 6.2	27-14-91-29
eClass 9.0	27-40-06-29		

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering data	<a href="#">EPLAN</a>
------------------	-----------------------