

ESG
ESG 9/17 MM GR**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 1429-0
Fax: +49 5231 14292083
www.weidmueller.com**Guaranteed long service life: ESG**

The multi-colour and multi-format labels have a strong adhesive layer to ensure the best possible adhesion to the underlying surface. Double laminated polyester makes the basic material very thin and yet extremely tear-resistant.

Your benefits with MultiMark

- Double laminated polyester
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

Type	ESG 9/17 MM GR
Order No.	2005230000
Version	ESG, Device markers, 17 x 9 mm, Grey
GTIN (EAN)	4050118390629
Qty.	3,000 pc(s).

Data sheet

ESG ESG 9/17 MM GR

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data

Dimensions and weights

Length	17 mm	Length (inches)	0.669 inch
Width	9 mm	Width (inches)	0.354 inch
Net weight	0.13 g		

General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	Grey	Length	17 mm
Material	Polyester	Number per roll	3,000
Operating temperature range, max.	120 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	V-0	Version	Self-adhesive, halogen-free
Width	9 mm		

Classifications

ETIM 6.0	EC001288	eClass 6.2	27-14-91-29
eClass 9.0	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering data	EPLAN, Zuken E3.S
------------------	-----------------------------------