

TM-I
TM-I 12 MM WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 1429-0

Fax: +49 5231 14292083

www.weidmueller.com

**Process reliability: TM-I**

TM-I inlay tags have a guide tab which allows them to slide easily into the transparent sleeves. Once the tag is in place, the tab is snapped off at the predetermined break point. The ready-assembled sleeves can then be simply pushed over the conductors. Your benefits: large quantities can be efficiently pre-assembled in a single step.

Your benefits with MultiMark

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

General ordering data

Type	TM-I 12 MM WS
Order No.	2005440000
Version	TM-I, Insert markers, 12 x 4 mm, White
GTIN (EAN)	4050118390278
Qty.	2,000 pc(s).

TM-I
TM-I 12 MM WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 1429-0

Fax: +49 5231 14292083

www.weidmueller.com

Technical data**Dimensions and weights**

Length	12 mm	Length (inches)	0.472 inch
Width	4 mm	Width (inches)	0.157 inch
Net weight	0.161 g		

General data

Colour	White	Length	12 mm
Material	Polyester	Number per roll	2,000
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	HB	Width	4 mm

Conductor and cable markers

Halogen	No
---------	----

Classifications

ETIM 6.0	EC001530	eClass 6.2	27-14-91-29
eClass 9.1	27-40-04-01		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering data	EPLAN
------------------	-----------------------