

**ESG**  
**ESG 6/17 MM WS****Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
www.weidmueller.com**Guaranteed long service life: ESG**

The multi-colour and multi-format labels have a strong adhesive layer to ensure the best possible adhesion to the underlying surface. Double laminated polyester makes the basic material very thin and yet extremely tear-resistant.

**Your benefits with MultiMark**

- Double laminated polyester
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

**General ordering data**

Type	ESG 6/17 MM WS
Order No.	<a href="#">2005 100000</a>
Version	ESG, Device markers, 17 x 6 mm, White
GTIN (EAN)	4050118390728
Qty.	3,000 pc(s).

## Data sheet

### ESG ESG 6/17 MM WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

## Technical data

### Dimensions and weights

Length	17 mm	Length (inches)	0.669 inch
Width	6 mm	Width (inches)	0.236 inch
Net weight	0.04 g		

### General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	White	Length	17 mm
Material	Polyester	Number per roll	3,000
Operating temperature range, max.	120 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	V-0	Version	Self-adhesive, halogen-free
Width	6 mm		

### Classifications

ETIM 6.0	EC001288	eClass 6.2	27-14-91-29
eClass 9.0	27-40-06-29		

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering data	<a href="#">EPLAN</a>
------------------	-----------------------