

**TM-I**  
**TM-I 18 MM WS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 1429-0  
Fax: +49 5231 14292083  
www.weidmueller.com

**Process reliability: TM-I**

TM-I inlay tags have a guide tab which allows them to slide easily into the transparent sleeves. Once the tag is in place, the tab is snapped off at the predetermined break point. The ready-assembled sleeves can then be simply pushed over the conductors. Your benefits: large quantities can be efficiently pre-assembled in a single step.

**Your benefits with MultiMark**

- Compact, practice-oriented range of products
- Quickly printed and assembled
- Reliable identification of your connections
- Excellent material properties

**General ordering data**

Type	TM-I 18 MM WS
Order No.	<a href="#">2005470000</a>
Version	TM-I, Insert markers, 18 x 4 mm, White
GTIN (EAN)	4050118390223
Qty.	2,000 pc(s).

**TM-I  
TM-I 18 MM WS**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 1429-0  
 Fax: +49 5231 14292083  
 www.weidmueller.com

**Technical data**
**Dimensions and weights**

Length	18 mm	Length (inches)	0.709 inch
Width	4 mm	Width (inches)	0.157 inch
Net weight	0.162 g		

**General data**

Colour	White	Length	18 mm
Material	Polyester	Number per roll	2,000
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	HB	Width	4 mm

**Conductor and cable markers**

Halogen	No
---------	----

**Classifications**

ETIM 6.0	EC001530	eClass 6.2	27-14-91-29
eClass 9.1	27-40-04-01		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering data	<a href="#">EPLAN, Zuken E3.S</a>
------------------	-----------------------------------