

**THM
EL 38 MM SI 30M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 1429-0

Fax: +49 5231 14292083

www.weidmueller.com

**Customised identification: EL**

The endless variations of MultiMark markers make them an economical alternative to conventional tag rails or special labels. For any given width, the length can be precisely configured by the software to match the respective markers perfectly. A blade is used to cut the labels individually to the specified size. Perfect for producing large labels for function blocks or complete terminal blocks.

Your benefits with MultiMark

- Double laminated polyester
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

Type	EL 38 MM SI 30M
Order No.	2006650000
Version	THM, Device markers, 30000 x 38 mm, Silver
GTIN (EAN)	4050118391558
Qty.	1 pc(s).

THM
EL 38 MM SI 30M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 1429-0
 Fax: +49 5231 14292083
 www.weidmueller.com

Technical data
Dimensions and weights

Length	30,000 mm	Length (inches)	1,181.1 inch
Width	38 mm	Width (inches)	1.496 inch
Net weight	330 g		

General data

Adhesive	Acrylate adhesive	Approval acc. to UL 969	Yes
Colour	Silver	Length	30,000 mm
Material	Polyester	Number per roll	1
Operating temperature range, max.	120 °C	Operating temperature range, min.	-40 °C
UL 94 flammability rating	V-0	Version	Self-adhesive, halogen-free
Width	38 mm		

Classifications

ETIM 6.0	EC001288	eClass 6.2	27-14-91-29
eClass 9.0	27-40-06-29		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering data	EPLAN
------------------	-----------------------