

## Wireless Combination Signalling device MP3



Product ref.: 142873A0  
**PRODUCT FEATURES**



- Acoustic reproduction of any desired sound files via loudspeaker
- Display of user-defined states with integrated multi-colour signal lamp
- Implementation of various functionalities is possible in connection with other Homematic devices and the Homematic WebUI
- The device can be used e.g. as doorbell or alarm signal if windows or doors are opened
- Individual MP3 files can be added to default sound clips (using a microSD/SDHC card)
- Easy to mount on walls or flexible use as standing unit

### TECHNICAL SPECIFICATIONS

Supply voltage:	2x 1.5 V LR14/baby/C
Battery life:	2 years (typ.)
Power consumption in standby:	max. 0.15 mA
Degree of protection:	IP20
Dimensions (W x H x D):	60 x 130 x 77 mm
Weight:	180 g (incl. batteries)
Radio frequency:	868.3 MHz
Typ. open area RF range:	120 m
File formats supported:	MP3 (CBR, VBR, ABR)
Bit rates supported:	32 / 320 Kbit/s
Memory cards supported:	FAT32 file system formatted microSD/microSDHC memory card, storage capacity up to 16 GB, performance up to class 10 with a max. number of 254 tracks

### LOGISTIC DATA

Product reference:	142873A0
EAN code:	4047976428731
Short description:	HM-OU-CFM-TW
Packing unit:	32
Packaging dimensions:	184 x 140 x 73 mm
Total weight:	564.6 g

### PACKAGE CONTENTS

Homematic Wireless Combination Signalling device MP3
2x 1.5 V LR14/baby/C batteries
Mounting material (2x screws and 2x plugs)
Wall mounting bracket
Operating manual in DE and EN