

## Wireless Door Viewer TX-75

Digital door viewer with built-in camera and 3.5" desk monitor



- Doorbell function
- Photo taking & Photo preview
- Data backup up to 100 photos (built-in storage)
- Portable desk monitor with 3.5" screen
- Camera with 300000 pixel & 170° wide angle view
- 2.4GHz wireless transmission ~200m open areas
- Power saving function
- USB charging function
- IP32 camera protection class (dripping water & <2.5mm impurity)
- "Do-it-yourself" installation, camera placement in peephole

### Technical Specifications Outdoor Camera & Emitter:

- 300000 pixels & 170° wide-angle
- Replaceable rechargeable lithium battery 7800mAh (type 18650)
- Charging time ~12 hours
- Working time ~39 hours continuously
- Standby time (monitoring mode) ~52 days
- Standby time (power saving mode) ~1 year [charge the battery min. every 6 month]
- Current consumption 160mA & power supply DC 5V/1A
- Operating temperature -10°C up to +50°C
- Weight / Dimensions: 280g / outline dimensions 3.6 x 0.8cm

### Technical Specifications Desk Monitor (Handset):

- 3.5" TFT colour LCD screen
- JPEG picture format
- 2.4GHz wireless connection mode
- Wireless transmission ~200m in open areas
- Replaceable rechargeable lithium battery 1100mAh (type BP-6M)
- Charging time ~3 hours
- Working time ~5 hours continuously
- Standby time ~6 days
- Desk charger for the monitor
- Current consumption 200mA & power supply DC 5V/1A
- Operating temperature 0°C up to +40°C
- Weight / Dimensions: 110g / outline dimensions 12.6 x 8.4 x 2.0cm

### Package Contents:

- Camera (wireless transmission)
- Emitter (providing the camera with power)
- 3.5" desk monitor (wireless reception)
- Desk charger for the monitor
- USB cable
- Power charger DC 5V
- Lithium 7800mAh battery type 18650
- Lithium 1100mAh battery type BP-6M
- Screw M4
- Steel board
- Round steel board
- User Manual

### Sold separately:

Replacement Battery for the Monitor 1100mAh (BP-6M): EAN Code 4260358121529, Article No. 4651  
Replacement Battery for the Emitter 7800mAh (type 18650): EAN Code 4260358121536, Article No. 4652

### EAN-Code:

4260358121581  
Article-No. 4648